Lumen Fécus

		}
•		

Project:
Location:
Cat. #:
Туре:
Quantity:

NEAR-UV 405 NM

FFR D 24 | LED Disinfection Retrofit Kit

Features:

- High performance disinfecting LED technology
- Continuously disinfect hard or soft surface, killing 99.9% of bacteria when lights are kept on
- Effective against MRSA, C. Difficile, Salmonella, E. Coli
- Completely harmless to humans and animals as the antibacterial spectrum is part of the normal visible LED spectrum (405nm near-UV wavelength)
- Field replaceable LED boards and drivers
- Frosted diffuser optimized to balance efficiency and aesthetics
- Quick and easy installation helps save on labor costs

• Buy American Act compliant (All base luminaires are BAA compliant. Addition of options may change eligibility. Contact factory for details.)

Applications:

Suitable for most commercial and institutional applications

- Office
- Retail
- Classrooms
- Healthcare Facilities
- Labs and clinics

Construction:

- Die-formed heavy-gauge cold rolled steel ballast housing with precision brake formed aluminum LED tray
- Frosted Polycarbonate Diffuser
- White enamel finish

Certifications:

• UL 1598 listed for US and Canada, suitable for damp locations



Warranty:

• 5 year limited system warranty see <u>www.LumenFocus.com</u> for complete warranty terms and conditions

Note: UVFocus products are designed utilizing proven anti-bacterial technology. 405nm near-UV light has been shown to substantially reduce bacterial presence. While these products can be considered disinfecting products, they should be used in conjunction with standard, proper disinfecting cleaning procedures to have the greatest impact for maintaining a clean environment. Successful UV disinfection requires a systems approach taking into account dose, optics and safety relevant to the specific application. Please consult with factory any questions or concerns.









© 2023 LumenFocus, LLC. LumenFocus reserves the right to change specifications without notice. Consult factory for most up to date specifications. www.lumenfocus.com | www.uvfocus.com 880 Facet Rd. | Henderson, NC 27537 252-430-6970 FFR_D_24_LED_v2.1 Page 1 of 3

example: FFR D 24 HI UV FA 840

Ordering Guide:

Size	Output	Voltage	Shielding	CRI/CCT	Options
24					- prioris
~7	++1		FA	840	
24 2x4	HI High	UV 120-277 34 347V	FA Frosted Acrylic	840 80 CRI / 4000K Disinfection LEDs	Blank No Options EM1 Emergency Kit - 12W 1200 nominal lumens ⁽¹⁾ F
					Fuse AR Plenum Ceiling Air Return BAA
			2x4 High 120-277 34	2x4 High 120-277 Frosted Acrylic 34 34 34 34 34	2x4 High 120-277 Frosted Acrylic 80 CRI / 4000K 34 34 Disinfection LEDs

BAA Buy American Act Compliant

⁽¹⁾ 120-277V only / 0°C-50°C ambient.

Performance Chart:

Catalog #	Watts	Lumens	LPW
FFR D 24 HI UV FA 840	81	7400	91.4

Schematic:



LUMENF©CUS Re-boardABILITY

The FFR D features field replaceable boards and drivers. This allows you to upgrade to more efficient technology in the future. Or, in the rare event of a failure, you can rapidly replace defective components. Re-boardABILITY helps to ensure you won't get stuck with an obsolete light fixture. Learn more about Re-boardABILITY here.





<u>Click here for a video demonstration of the</u> <u>re-boarding process on a FFL.</u> Note: Exact time varies depending on the model.



© 2023 LumenFocus, LLC. LumenFocus reserves the right to change specifications without notice. Consult factory for most up to date specifications. www.lumenfocus.com | www.uvfocus.com 880 Facet Rd. | Henderson, NC 27537 252-430-6970

UVF*cus

Installation Instructions:



1) Turn off power to luminaire, remove all fluorescent components, dispose of properly.



2) Insert endcaps between ceiling grid and troffer.



3) Slide LED panel between grid and troffer, fasten with provided quarter turns.



4) Connect LED panel with provided disconnect. Insert blank side panel between grid and troffer, fasten with provided quarter turns.



5) Insert lens material into track, turn on power.



Installation Demo Online:

An online demonstration video can be found on our YouTube channel <u>at this link.</u>







www.lumenfocus.com | www.uvfocus.com 880 Facet Rd. | Henderson, NC 27537 252-430-6970